Hydrogen Generators

for GC and GC/MS carrier gas applications



The Parker domnick hunter H-MD ultra high purity hydrogen gas generators offer the optimum combination of safe operation, reliability, performance and low cost of ownership.

Utilising field proven PEM cell technology, hydrogen is produced on demand from deionised water and electricity, at low pressure and with minimal stored volume. Innovative control software allows unrivalled operational safety and reliability.

The H-MD generators ideally supply GC and GC/MS carrier gas, in addition to all known combustion detectors that are routinely used in today's laboratory workflows. Four models operate at flow rates; 160 ml/min, 250 ml/min, 500 ml/min and 1100 ml/min.

Hydrogen generators are available with Remote Networking software. RemoteNet allows up to 27 hydrogen generators to be actively controlled from one central PC, and facilitates true cascading capabilities.



Contact Information:

Parker Hannifin Ltd. domnick hunter Industrial Division Dukesway, Team Valley Trading Estate Gateshead, Tyne and Wear England NE11 0PZ

Tel: +44 (0)191 402 9000 Fax: +44 (0)191 482 6296 Email: gasgen@parker.com www.domnickhunter.com

Product Features:

- Eliminate dangerous hydrogen cylinders from the work place
- Simple to install and operate
- Compact, reliable with minimal maintenance
- Produces a continuous supply of 99.99995% pure hydrogen up to 1,100ml/min and 6.9 bar
- · 2 year standard cell warranty
- Optional automatic water fill and remote networking capability



Product Selection

Model	Flow Rate	Purity*	Water Consumption (24/7, full flow)	Delivery Pressure		Optional Auto	
	ml/min	%	L/week	bar g	psi g	Water Fill (AWF)	
20H-MD	160	>99.99995	1.69	0.69-6.89	10-100	YES	
40H-MD	250	>99.99995	2.41	0.69-6.89	10-100	YES	
60H-MD	500	>99.99995	4.82	0.69-6.89	10-100	YES	
110H-MD	1100	>99.99995	10.60	0.69-6.89	10-100	Standard	

^{*}With respect to oxygen

Note: For auto water fill option add suffix AWF ie 20H-MD-AWF

Technical Data

Ambient Temperature Range	5 - 40°C 41 - 104°F		
Water Supply Pressure*	0.1 bar g 1.45 psi g		
Water Supply Flow Rate*	1 L/min		
Water Quality	Deionised. ASTM II, >1M $\Omega,$ <1 $\mu s,$ filtered to <100 μm		
Supply Voltage Range	90V - 264V 50/60Hz		
Port Connections Hydrogen Outlet Water Drain Water Fill*	¹ /a" Compression Fitting Quick Release Push in Fitting Quick Release Push in Fitting		

^{*}With optional AWF

Weights and Dimensions

Model	Height (H)		Width (W)		Depth (D)		Weight (Empty)		Weight (Full of Water)	
	mm	in	mm	in	mm	in	kg	lb	kg	lb
20H-MD	456	17.9	342	13.5	470	18.5	20.5	45.2	25	55.1
40H-MD	456	17.9	342	13.5	470	18.5	20.5	45.2	25	55.1
60H-MD	456	17.9	342	13.5	470	18.5	20.5	45.2	25	55.1
110H-MD	456	17.9	342	13.5	470	18.5	23.6	51.8	28	61.7

Preventative Maintenance

Preventative Maintenance Kit	Part Number	Change Frequency
6 Month Kit	604971500	6 Months
24 Month Kit	604970720	24 Months

Optional Extra's

Description	Part Number	Required for
RemoteNet user software	604971510	up to two generators
RemoteNet user add on kit	604971520	each additional generator (604971510 required)

©2011 Parker Hannifin Corporation. All rights reserved.

Catalogue: 174004750_01_EN 03/11

